

Monteringsbar smart LED-huvudlampa med Bluetooth®-anslutning. Boost-läge ger upp till 1000 lumen. Optisense™-tekniken justerar själv ljusstyrkan efter ljusförhållandena. Monteras på lampklammorna på alla KASK-hjälmars. Multicolor LED head light with boost up to 600 lumens with rechargeable batteries. Mounts to lamp clips on all KASK helmets.

WLA00002



TECHNICAL DETAILS

Weight including Battery	98 g
Maximum light output boost	600 lm for 10"
Light output max - min	400 lm 170 lm 20 lm
Runtime min - max	7 h 10 h 60 h
Battery	1* Li-ion (included) or 2*AA Alkaline 1.5V/ 2*AANiMH1.2V (not included)
IP class	IP54
Charging time	270 min (according to hardware used)
Light functions	Low power, mid power, power, blink, boost
Functions	Low battery warning; charge indicator; battery indicator; rapid focus; transport lock; red green and blue light.
Included with headlamp	Headlamp + Elastic Band Overhead-band Charging cable Battery (to be installed)

TECHNOLOGIES



ADVANCED FOCUS SYSTEM®

Patented technology that allows a seamless transition from broad low beam to sharply focused high beam.



RAPID FOCUS

Mechanism that allows the light beam to be adjusted quickly.



TRANSPORTATION LOCK

Prevents the light from being turned on inadvertently.



MAGNETIC CHARGE SYSTEM

Easily recharge the lithium-ion battery via a magnetic USB cable.



COOLING TECHNOLOGY

Dissipates heat generated by extended headlamp use.



DUAL POWER SOURCE

Equipped with two battery types; a rechargeable lithium-ion battery and regular AA alkaline battery.



RED READING LIGHT

Equipped with a red LED light for better nighttime visibility and emergency situations.



GREEN LIGHT

Equipped with a green LED light for increased run time and nighttime visibility.



BLUE LIGHT

Equipped with a blue LED light for use in fog and smoky conditions.

MOUNTING OPTIONS

OVERHEAD-BAND MOUNTING (INCLUDED WITH HEADLAMP)



FRONT ATTACHMENT MOUNTING (ADAPTER NOT INCLUDED WITH HEADLAMP)



* Images of headlamps are for illustrative purposes.

ADDITIONAL INFORMATION

GUARANTEE

2 years starting from the date of purchase.

CLEANING

Use a damp clean cloth and dry carefully. Do not use chemical detergents, solvents, petrol powders as they are too aggressive and could lower the structural resistance of the components.

2
YEARS
GUARANTEE



SCAN FOR COMPLETE COLLECTION